



BYO Premium and BYO Premium Toric are custom-made silicone hydrogel soft contact lenses for 3 monthly replacement. The progressive aspherical back surface geometry makes this design unique and guarantees comfort and optimal movement of the lens. The Premium material (silicone hydrogel) guarantees an excellent DK/t for Daily Wear. This makes the lens suitable for high powers. The combination of prismatic and dynamic stabilization makes the lens very suitable for even higher degrees of astigmatism.

The unique geometry in combination with the silicone hydrogel material makes the BYO Premium and the BYO Premium Toric suitable for all grades of ametropia.

All lenses are laser marked with Procornea logo and unique batch number. This means guaranteed quality.

### BYO Premium and BYO Premium Toric are also available as multifocals

Check the designated datasheets for BYO Premium Zoom and BYO Premium Toric Zoom.

### Application

An ideal 3-monthly lens. Also suitable for long periods of wear and use in a dry environment.

### Highlights

- Custom-made
- Silicone hydrogel
- Good stabilization
- Stable vision
- 3-monthly replacement

### Fitting advice

BCR = Kmean + 0.60 mm

### Parameter range BYO Premium and BYO Premium Toric

Radius (r0):	7.50 mm to 9.80 mm in 0.10 mm steps
Sphere Power (Fv):	+25.00 D to -25.00 D in 0.25 D steps
Cylinder (Toric):	-0.75 D to -6.00 D in 0.25 D steps
Axis (Toric):	0° to 180° per 1°
Diameter (øT)*:	13.50 mm to 15.00 mm in 0.10 mm steps

**\*Standard 14.00 mm. Special parameters on request**

### Technical information

Material:	Ultima silicone hydrogel*	GM3
Water content:	48%	58%
Dk/t:	71 (-3.00 D)	27 (-3.00 D)
Modulus:	0.62 Mpa	0.16 Mpa
UV filter:	Yes	Yes
Handling tint:	No	Clear/Blue
Central thickness:	0.30 mm (-3.00 D)	0.10 mm (-3.00D)
Marking (Toric):	Two markings at 3 and 9 o'clock	
Engravings:	The unique serial number and Procornea logo	
Application:	Daily wear	
Packaging:	Blister	

**\* Standard material**



# BYO Premium Zoom and BYO Premium Toric Zoom

BYO Premium zoom and BYO Premium Toric zoom are custom-made multifocal silicone hydrogel soft contact lenses for 3 monthly replacement. The progressive aspherical back surface geometry makes this design unique and guarantees comfort and optimal movement of the lens. The aberration free front- optics and the sophisticated addition profile provide clear vision at each distance. This means a good functional vision at all times. The Ultima silicone hydrogel material guarantees an excellent DK/t for Daily Wear. This makes the lens especially suitable for high grades of ametropia.

The BYO Premium and BYO Premium Toric Zoom are both available in a Centre Near (CN) and a Centre Distance (CD) profile. The combination of prismatic and dynamic stabilization makes the lens unique and very suitable for even higher degrees of astigmatism.

All lenses are laser marked with Procornea logo and unique batch number. This means guaranteed quality.

### Application

An ideal 3-monthly lens. Also suitable for long periods of wear and use in a dry environment.

### Highlights

- Custom-made
- Silicone hydrogel
- Good stabilization
- Perfect multifocal optics
- Good functional vision at each distance
- No visible transitions
- AB-technology
- 3-monthly replacement
- Standard Centre Near, also available in Centre Distance.

### Fitting advice

BCR = Kmean + 0.60 mm

### Parameter range BYO Premium and BYO Premium Toric

Radius (r0):	7.50 mm to 9.80 mm in 0.10 mm steps
Sphere Power (Fv):	+25.00 D to -25.00 D in 0.25 D steps
Cylinder (Toric):	-0.75 D to -6.00 D in 0.25 D steps
Axis (Toric):	0° to 180° per 1°
Reading addition	+0.75 D to +3.00 D in 0.25 D steps
Diameter (øT)*:	13.50 mm to 15.00 mm in 0.10 mm steps

**\*Standard 14.00 mm. Special parameters on request**

### Technical information

Material:	Ultima silicone hydrogel*	GM3
Water content:	48%	58%
Dk/t:	71 (-3.00 D)	27 (-3.00 D)
Modulus:	0.62 Mpa	0.16 Mpa
UV filter:	Yes	Yes
Handling tint:	No	Clear/Blue
Central thickness:	0.30 mm (-3.00 D)	0.10 mm (-3.00D)
Marking (Toric):	Two markings at 3 and 9 o'clock	
Engravings:	The unique serial number and Procornea logo	
Application:	Daily wear	
Packaging:	Blister	

**\* Standard material**

